

EPIC® MC 2.5 contatos estampados em carretel

para insertos e módulos dos conectores retangulares EPIC®

The stamped contacts are coiled up in reels of 100 or 200 pieces for use with conductor cross-sections from 0.5 to 1.5 mm² and 1.5 to 2.5 mm².

Info

Contatos branhados em prata e passivados
for very fast crimping with Hand crimping tool for contacts on reel
Two crimp areas with wire and insulation crimp



Características do produto

Stamped crimping contact silver plated on small reel
use Hand crimping tool 11147005 for cross section from 0.5 to 1.5mm²
use Hand crimping tool 11147006 for cross section from 1.5 to 2.5mm²

Dados técnicos

Classificação ETIM 5:

Classe-ID ETIM 5.0: EC000796

Descrição de Classe ETIM 5.0: Contatos para conectores industriais

Classificação ETIM 6:

ID da classe ETIM 6.0: EC000796

Descrição da classe ETIM 6.0: Contato para conectores industriais

Observação

As imagens e gráficos demonstradas não são reprodução fiel do produto, são meramente ilustrativos
Os preços são preços líquidos sem IVA e sobretaxas. Venda apenas para clientes empresariais.

EPIC® MC 2.5 contatos estampados em carretei

Código do Produto	Descrição do artigo	Tipo de contato	Seção transversal do condutor em mm ²	Superfície	Comprimento de decapagem (mm)	Observação	Unidade de embalagem
Contatos							
11208000	EPIC® MC SCBG AG 0.5-1.5 200 LI	Macho	0.5 - 1.5	Ag	3,5 + 0,5	1 bobina (emb.) = 200 contatos	1
11209000	EPIC® MC BCBG AG 0.5-1.5 200 LI	Fêmea	0.5 - 1.5	Ag	3,5 + 0,5	1 bobina (emb.) = 200 contatos	1
11208500	EPIC® MC SCBG AG 1.5-2.5 100 LI	Macho	1.5 - 2.5	Ag	3,5 + 0,5	1 bobina (emb.) = 100 contatos	1
11209500	EPIC® MC BCBG AG 1.5-2.5 100 LI	Fêmea	1.5 - 2.5	Ag	3,5 + 0,5	1 bobina (emb.) = 100 contatos	1

Última atualização (22.07.2024)

©2024 Lapp Group - all rights reserved.

Gestão de Produtos <http://lappbrasil.lappgroup.com>

Você pode encontrar os dados técnicos atuais na folha de dados correspondente.

PN 0456 / 02_03.16