

## SKINTOP® ST-M L-BOXX

Being organised is essential. With our product case for SKINTOP® ST-M cable glands with a component insert and transparent lid, you always have the right thread size at hand. Thanks to its robust design, integration in vehicle equipment systems and the snap-in system for combination with other cases, it is perfectly suited for assembly use.



### Vantagens

Inset for loose components ensures optimum organisation and prevents mixing of the items.  
Case made of light and robust, shock- and impact-resistant ABS plastic.  
Intelligent snap system allows quick connection, combination and disconnection of cases, saving time and energy during transport.  
Easy integration in vehicle equipment systems of numerous manufacturers.  
Transparent lid allows a perfect overview even when closed.

### Âmbitos de aplicação

For safe transport and storage of SKINTOP® ST-M cable glands (sizes M12 to M32).  
Especially for assembly use, e.g. on the construction site.

### Características do produto

Two robust locking mechanisms ensure a secure closure.  
Case can be refilled with standard packaging units.  
Mounting instruction and locknut included.

### Escopo de fornecimento

SKINTOP® ST-M M12 / 50 pieces  
SKINTOP® ST-M M16 / 50 pieces  
SKINTOP® ST-M M20 / 25 pieces  
SKINTOP® ST-M M25 / 25 pieces  
SKINTOP® ST-M M32 / 5 pieces  
Counter nut SKINTOP® GMP-GL-M included

### Dados técnicos

Classificação ETIM 5:

ETIM 5.0 Class-ID: EC000441

Descrição de classe ETIM 5.0: Prensa-cabo rosqueado

Classificação ETIM 6:

ID da classe ETIM 6.0: EC000441

Descrição da classe ETIM 6.0: Prensa-cabos

Cor de fornecimento:

RAL 7001 cinza prateado

RAL 7035 cinza claro

RAL 9005 preto

Última atualização (26.04.2024)

©2024 Lapp Group - all rights reserved.

Gestão de Produtos <http://lappbrasil.lappgroup.com>

Você pode encontrar os dados técnicos atuais na folha de dados correspondente.

PN 0456 / 02\_03.16

## SKINTOP® ST-M L-BOXX

### Observação

As imagens e gráficos demonstradas não são reprodução fiel do produto, são meramente ilustrativos  
Os preços são preços líquidos sem IVA e sobretaxas. Venda apenas para clientes empresariais.



## SKINTOP® ST-M L-BOXX

Código do Produto	Descrição do Produto / Tamanho	Ø F mm	Emb.
53110050	SKINTOP® ST-M L-BOXX (SGY)	-	1
53110051	SKINTOP® ST-M L-BOXX (LGY)	-	1
53110052	SKINTOP® ST-M L-BOXX (BK)	-	1

Última atualização (26.04.2024)

©2024 Lapp Group - all rights reserved.

Gestão de Produtos <http://lappbrasil.lappgroup.com>

Você pode encontrar os dados técnicos atuais na folha de dados correspondente.

PN 0456 / 02\_03.16