

EPIC® H-D 1.6 Contatos usados

para insertos e módulos dos conectores retangulares EPIC®

Machined EPIC H-D contacts are suitable for industrial data and signal transmission. Silver or gold plating guarantee reliable contacting.

Info

High quality contacts for data and signal transmission with 1.6mm
Choice of silver or gold plating



Características do produto

High quality contacts for data and signal transmission with 1.6mm

Choice of silver or gold plating

Connection cross sections from 0.14mm² to 2.5mm² available for combined data and power transmission

With the appropriate tools, good contacting is created quickly and easily

Dados técnicos

Classificação ETIM 5:

Classe-ID ETIM 5.0: EC000796

Descrição de Classe ETIM 5.0: Contatos para conectores industriais

Classificação ETIM 6:

ID da classe ETIM 6.0: EC000796

Descrição da classe ETIM 6.0: Contato para conectores industriais

Observação

As imagens e gráficos demonstradas não são reprodução fiel do produto, são meramente ilustrativos

Os preços são preços líquidos sem IVA e sobretaxas. Venda apenas para clientes empresariais.

EPIC® H-D 1.6 Contatos usados

Código do Produto	Descrição do artigo	Tipo de contato	Seção transversal do condutor em mm ²	Cross-section identification	Superfície	Comprimento de decapagem (mm)	Peça/emb.
Contatos							
13162000	H-D 1.6 usinado	Macho	0.14 - 0.37	1	Ag	8,0	100
13163000	H-D 1.6 usinado	Fêmea	0.14 - 0.37	1	Ag	8,0	100
13162100	H-D 1.6 usinado	Macho	0.5	2	Ag	8,0	100
13163100	H-D 1.6 usinado	Fêmea	0.5	2	Ag	8,0	100
13162200	H-D 1.6 usinado	Macho	0.75 - 1	3	Ag	8,0	100
13163200	H-D 1.6 usinado	Fêmea	0.75 - 1	3	Ag	8,0	100
13162300	H-D 1.6 usinado	Macho	1.5	4	Ag	8,0	100
13163300	H-D 1.6 usinado	Fêmea	1.5	4	Ag	8,0	100
13162400	H-D 1.6 usinado	Macho	2.5	5	Ag	5,8	100
13163400	H-D 1.6 usinado	Fêmea	2.5	5	Ag	5,8	100
13162500	H-D 1.6 usinado	Macho	0.14 - 0.37	1	Au	8,0	100
13163500	H-D 1.6 usinado	Fêmea	0.14 - 0.37	1	Au	8,0	100
13162600	H-D 1.6 usinado	Macho	0.5	2	Au	8,0	100
13163600	H-D 1.6 usinado	Fêmea	0.5	2	Au	8,0	100
13162700	H-D 1.6 usinado	Macho	0.75 - 1	3	Au	8,0	100
13163700	H-D 1.6 usinado	Fêmea	0.75 - 1	3	Au	8,0	100
13162800	H-D 1.6 usinado	Macho	1.5	4	Au	8,0	100
13163800	H-D 1.6 usinado	Fêmea	1.5	4	Au	8,0	100
13162900	H-D 1.6 usinado	Macho	2.5	5	Au	5,8	100
13163900	H-D 1.6 usinado	Fêmea	2.5	5	Au	5,8	100

EPIC® H-D 1.6 Contatos usinados