

SKINDICHT® MA-PG/M

SKINDICHT® MA-PG/M, adaptador de latão niquelado com rosca de conexão PG como adaptador de uma rosca externa PG para uma rosca interna métrica

Vantagens

Allows easy transition from a PG external thread to a metric internal thread.

Withstands temperatures up to +200 °C.

Available for thread sizes till PG36/M40.

Mold A in easy-grip knurled design for easy screwing in of the adapter even in oily environments; mold B in smooth design.

Article numbers ending in "LF" are lead-free product alternatives with the same product properties. "Lead-free" articles do not contain lead, which is currently still allowed to make up to four percent in copper alloys. It could be banned in the future according to the RoHS Directive.

Âmbitos de aplicação

For applications with different types of threads.

Withstands high chemical and mechanical stress.

Suitable for outdoor use.

Projeto do produto

Rosca de conexão PG

Projeto do produto

Forma A: Serrilhada

Forma B: Lisa

Dados técnicos

Classificação ETIM 5:

ETIM 5.0 Class-ID: EC000441

Descrição de classe ETIM 5.0: Prensa-cabo rosqueado

Classificação ETIM 6:

ID da classe ETIM 6.0: EC000441

Descrição da classe ETIM 6.0: Prensa-cabos

Material:

Latão, niquelado

Faixa de temperatura:

-60 °C até +200 °C

Observação

As imagens e gráficos demonstradas não são reprodução fiel do produto, são meramente ilustrativos

Os preços são preços líquidos sem IVA e sobretaxas. Venda apenas para clientes empresariais.

SKINDICHT® MA-PG/M

Código do Produto	Forma	Tamanho PG	Rosca interna M2	Peça/emb.
SKINDICHT® MA-PG/M				
52104490	B	7	12 x 1,5	100
52104491	B	9	16 x 1,5	50
52104492	A	11	16 x 1,5	50
52104493	B	11	20 x 1,5	50
52104494	B	13,5	20 x 1,5	50
52104495	A	16	20 x 1,5	50
52104495LF	A	16	20 x 1,5	50
52104496	B	16	25 x 1,5	50
52104497	A	21	20 x 1,5	50
52104498	A	21	25 x 1,5	50
52104499	B	21	32 x 1,5	50
52104500	A	29	25 x 1,5	25
52104501	A	29	32 x 1,5	25
52104502	B	29	40 x 1,5	10
52104503	A	36	40 x 1,5	10
52104490LF	B	7	12 x 1,5	100
52104491LF	B	9	16 x 1,5	50
52104492LF	A	11	16 x 1,5	50
52104493LF	B	11	20 x 1,5	50
52104494LF	B	13,5	20 x 1,5	50
52104496LF	B	16	25 x 1,5	50
52104497LF	A	21	20 x 1,5	50
52104498LF	A	21	25 x 1,5	50
52104499LF	B	21	32 x 1,5	50
52104500LF	A	29	25 x 1,5	25
52104501LF	A	29	32 x 1,5	25
52104502LF	B	29	40 x 1,5	10
52104503LF	A	36	40 x 1,5	10

Última atualização (25.08.2024)

©2024 Lapp Group - all rights reserved.

Gestão de Produtos <http://lappbrasil.lappgroup.com>

Você pode encontrar os dados técnicos atuais na folha de dados correspondente.

PN 0456 / 02_03_16