

FLEXIMARK® THERMO SPOT

Temperature indicator for monitoring electrical equipment, with memory effect, activation temperature of +52°C.



Engenharia de máquinas e instalações



Tempo de montagem

Vantagens

The attached temperature indicators make it possible to carry out a visual inspection of electrical equipment with a flat surface. A colour change occurs if the temperature is exceeded.

Quickly identifying overheated electrical components makes rapid cause analysis possible. This allows appropriate countermeasures to be initiated to avoid plant downtimes.

24/7 monitoring and the memory effect make it possible to continuously record temperature exceedance, and can act as an early warning of overheating.

Safe, fast and uncomplicated installation.

Available in different packaging units.

Âmbitos de aplicação

For indicating that temperatures have been exceeded.

Irreversible colour change at temperatures from +52°C.

For use with electrical equipment.

Can be used in dry interiors.

Observação

Limitations: These labels will not prevent electrical faults or fires but will aid in monitoring abnormal temperatures and will give visual indication of potential electrical faults and fire risks. These labels do not replace the need to formally install, test, inspect and maintain electrical installations as per the electricity at work act, the electrical installation wiring regulations and manufacturer's instructions.

Dados técnicos

Classificação ETIM 5:

EC003592

Cor de fornecimento:

Branco

Material:

Polyester.

Covering film: Polyester

Adhesive: Acrylic

Color change material: Non-toxic, white crystalline solid on a black absorbent backing, adhered with acrylic adhesive.

Faixa de temperatura:

- Activation temperature: 52°C

- Tolerance: +/- 1°C

- Store at room temperature & humidity
(i.e. 16°C to 27°C & 40% to 60% RH)

Observação

As imagens e gráficos demonstradas não são reprodução fiel do produto, são meramente ilustrativos

Os preços são preços líquidos sem IVA e sobretaxas. Venda apenas para clientes empresariais.

FLEXIMARK® produtos são vendidos em unidades de embalagem. Como exemplo, se você gostaria de um pedido 640 rótulos de 32 LCK você só precisa encomendar um PU em vez de 640 rótulos individuais.



FLEXIMARK® THERMO SPOT

Código do Produto	Descrição do Produto	Tamanho (mm)	Emb.
83881128	FLEXIMARK® THERMO SPOT 52°C - 1000	Ø17	1000
83881129	FLEXIMARK® THERMO SPOT 52°C - 200	Ø17	200
83881130	FLEXIMARK® THERMO SPOT 52°C - 50	Ø17	50
83881131	FLEXIMARK® THERMO SPOT 52°C - 20	Ø17	20