

ETHERLINE® ACCESS U IP67

Unmanaged industrial Ethernet switch for decentralised applications.

Switches de rede industriais para soluções baseados em Ethernet na Smart Factory.

Info

IP 67

compatible for PROFINET® networks



Componentes de automação complementares da LAPP



Engenharia de máquinas e instalações

Vantagens

With 8 ports (10/100Base-T(X)) for D-coded M12 connectors.

Particularly suitable for harsh environments thanks to protection class IP 67.

Quickly ready for use with little installation effort.

High performance due to generous 16K MAC address table and extensive 256Kbyte packet buffer.

Âmbitos de aplicação

For use in Ethernet-based automation technology networks.

Also suitable for use in PROFINET networks ("Conformance Class A").

For decentralised use at field level, outside the control Cabinet.

Can be used in an extended temperature range from -40 °C to +75 °C.

Dados técnicos

power supply: DC 24 V (18-30 V DC)

Tipo de proteção: IP 67

Faixa de temperatura: -40 °C up to +75 °C

ETHERLINE® ACCESS U IP67

Observação

PROFINET® é uma marca registrada da PNO (organização de usuários PROFIBUS)

As imagens e gráficos demonstradas não são reprodução fiel do produto, são meramente ilustrativos

Os preços são preços líquidos sem IVA e sobretaxas. Venda apenas para clientes empresariais.



ETHERLINE® ACCESS U IP67

Código do Produto
21700148

Última atualização (07.05.2024)

©2024 Lapp Group - all rights reserved.

Gestão de Produtos <http://lappbrasil.lappgroup.com>

Você pode encontrar os dados técnicos atuais na folha de dados correspondente.

PN 0456 / 02_03.16