

EPIC® ASC axial screw contact

para insertos e módulos dos conectores retangulares EPIC®

Axial screw contact for high current module modul EPIC® MH 1 250A, suitable for cross section from 35mm² up to 70mm², service-friendly connection without any special tool.

Info

EPIC® ASC contact as an alternative to the crimping contact.
Axial screw contact for assembly with low-cost tools.



Componentes de automação complementares da LAPP



Alimento e Bebidas



Engenharia de máquinas e instalações



Energia Eólica



Escala de aperto mais ampla



Tempo de montagem

Âmbitos de aplicação

Axial screw contact that can be freely rotated in the high-current module simplifies assembly, prevents torsional stress and thus ensures contact reliability between contact and wire.

Assembly of the contact outside the module enables visual inspection of the connection and thus eliminates the failure potential of insufficient overlapping between contact and wire.

Silver-plated contact surface for low contact resistance and minimal heat generation at the contact.

Características do produto

Axial screw clamp technology allows service-friendly connection without special crimping tool, saves costs and is suitable for removable connections.

Simple conductor connection by means of hexagon socket and open-end wrench.

Only one axial screw contact required for conductor cross-sections from 35 to 70 mm².

Última atualização (22.07.2024)

©2024 Lapp Group - all rights reserved.

Gestão de Produtos <http://lappbrasil.lappgroup.com>

Você pode encontrar os dados técnicos atuais na folha de dados correspondente.

PN 0456 / 02_03.16

EPIC® ASC axial screw contact

Axial screw contact can be used in existing high-current module as an alternative to crimp contact.
Connection of the high-current module with axial screw contact ensures maximum safety for the user due to contact protection.

Dados técnicos

Resistência de contato:	< 0.3 mOhm
Terminação do cabo:	Crimp termination: 35 mm ² ... 70 mm ²
Material:	brass silver plated CuZn / Ag
Ciclos de operação mecânica:	500
Faixa de temperatura:	-40°C a +120°C

Observação

As imagens e gráficos demonstradas não são reprodução fiel do produto, são meramente ilustrativos
Os preços são preços líquidos sem IVA e sobretaxas. Venda apenas para clientes empresariais.

EPIC® ASC axial screw contact

Código do Produto	Descrição do artigo	Versão	Unidade de embalagem
44423397	EPIC® ASC SSEM AG 35-70mm ² D=10.0mm	Conector	10
44423396	EPIC® ASC BSEM AG 35-70mm ² D=10.0mm	Fêmea	10

Última atualização (22.07.2024)

©2024 Lapp Group - all rights reserved.

Gestão de Produtos <http://lappbrasil.lappgroup.com>

Você pode encontrar os dados técnicos atuais na folha de dados correspondente.

PN 0456 / 02_03.16