

SKINDICHT® SM-PE-M

SKINDICHT® SM-PE-M, counter nuts with cutting edges to cut through the insulating layer, thus guaranteeing an optimum EMC contact



Boa resistência química



Resistência mecânica

Vantagens

Optimum contacting of a coated enclosure for protection against electromagnetic interference and for equipotential bonding. Contact is achieved when the locknut is tightened by the cutting edges scratching the coated layer of the housing.

Withstands temperatures up to +200 °C.

Apropriado para todos os prensa-cabos métricos nas aplicações de aterramento e IEC

Article numbers ending in "LF" are lead-free product alternatives with the same product properties. "Lead-free" articles do not contain lead, which is currently still allowed to make up to four percent in copper alloys. It could be banned in the future according to the RoHS Directive.

Âmbitos de aplicação

For use on the inside of painted, anodised or powder-coated enclosures.

Can be used with metric SKINTOP® and SKINDICHT® cable glands for applications where electromagnetic compatibility (EMC) is required.

Withstands high chemical and mechanical stress.

Projeto do produto

Rosca de conexão métrica de acordo com DIN EN 60423

Base para especificações técnicas DIN IEC 62444

Dados técnicos

Classificação ETIM 5:

ETIM 5.0 Class-ID: EC000940

Descrição de classe ETIM 5.0: Contra porca para prensa-cabo rosqueado

Classificação ETIM 6:

ID da classe ETIM 6.0: EC000940

Última atualização (26.04.2024)

©2024 Lapp Group - all rights reserved.

Gestão de Produtos <http://lappbrasil.lappgroup.com>

Você pode encontrar os dados técnicos atuais na folha de dados correspondente.

PN 0456 / 02_03.16

SKINDICHT® SM-PE-M

Material:

Descrição da classe ETIM 6.0: Contraporca para prensa-cabos

Latão, niquelado

Faixa de temperatura:

-60 °C até +200 °C

Observação

As imagens e gráficos demonstradas não são reprodução fiel do produto, são meramente ilustrativos
Os preços são preços líquidos sem IVA e sobretaxas. Venda apenas para clientes empresariais.

SKINDICHT® SM-PE-M

Código do Produto	Descrição do Produto / Tamanho	Espessura mm	SW wrench size mm	Ø externo mm	Peça/emb.
SKINDICHT® SM-PE-M					
52103300	M 12 x 1,5	4.7	15	17.3	100
52103310	M 16 x 1,5	4.7	19	21.9	100
52103320	M 20 x 1,5	4.7	24	27.7	100
52103330	M 25 x 1,5	5.2	30	34.6	50
52103340	M 32 x 1,5	5.7	36	41.5	50
52103350	M 40 x 1,5	6.5	46	53.1	25
52103360	M 50 x 1,5	6.5	60	69.3	10
52103370	M 63 x 1,5	7.0	70	80.8	10
52103371	M 75 x 1,5	8.0	85	95.0	1
52006494	M 72 x 2	10.0	85	98.0	1
52103372	M 90 x 2	10.0	102	114.0	1
52103373	M 110 x 2	12.0	124	135.0	1
52103300LF	M 12 x 1,5	4.7	15	17.3	100
52103310LF	M 16 x 1,5	4.7	19	21.9	100
52103320LF	M 20 x 1,5	4.7	24	27.7	100
52103330LF	M 25 x 1,5	5.2	30	34.6	50
52103340LF	M 32 x 1,5	5.7	36	41.5	50
52103350LF	M 40 x 1,5	6.5	46	53.1	25
52103360LF	M 50 x 1,5	6.5	60	69.3	10
52103370LF	M 63 x 1,5	7.0	70	80.8	10

Última atualização (26.04.2024)

©2024 Lapp Group - all rights reserved.

Gestão de Produtos <http://lappbrasil.lappgroup.com>

Você pode encontrar os dados técnicos atuais na folha de dados correspondente.

PN 0456 / 02_03.16